





INTRODUCTION

To detach the fruitlets from the sterilized fruit bunch.

CONSTRUCTION

- 4 columns are provided with MS channel ties.
- Side panel plate using MS plate with openable service door and chute.
- Top operating platform using MS chequer plate, support beam and handrails.
- Shafted Rotating drum are support with 2 units of heavy duty bearings at both ends of the shaft
- Shaftless rotating drums are support with 4 sets of cast steel roller c/w stopper.
- Drums are using MS plate cut into rings/spider arm (shafted) c/w longitudinal MS flat bar. Lifter provided inside drum to lift up bunches.



DESCRIPTION

Size : 10 tons, 20 tons, 30 tons, 45 tons,

60 tons

Drive : Gear head powered by motor

with belt and pulley.

Final operating drum speed of

22-25 rpm

Others : Double drum threshing machine

can be provided

For further information, please contact sales office, or:



Excelmech Engineering Sdn. Bhd. (Company No. 862039-X)

Lot 2828, Jln Kelkati 32/168, Off Jln. Sri Gambut Bukit Naga, Seksyen 32, 40460 Shah Alam, Selangor Darul Ehsan, Malaysia. Tel: 603-5167 1589 Fax: 603-5167 2588 E-mail: contact@excelmech.com.my

